High Performance 100% Neutral Anti-Fungal Silicone

SFALANT 4588T

SEALANT 4588T: High performance neutral cure silicone rubber with excellence anti-mold / anti mildew properties when exposed to moisture and humidity at room temperature. Due to its non-saq, non-flowable features, it may be applied overhead or on sidewall joint surface. It presents no offensive odor during curing and will not corrode metals. Discoloration of copper based metals may occur when hermetically sealed. Moreover, it can adhere well on alkaline material such as mortar and white cement.

Feature

- Excellent anti-mold / anti mildew properties.
- One-component paste-liked silicone sealant
- General purposes for sealing and bonding with various types of materials
- No corrosion for many substances and low oxime odor
- Curing at room temperature and easy handling
- Weatherbility resistance at -50 to 150°C

- General purpose sealing and bonding applications with superior anti-mold / anti mildew properties.
- Suitable for various substrate such as Glass Metals Sashes Marbles -Prefab housing units - Suspension construction - Mortar - Stone - Bath tubs, sinks, kitchen tubs, and sealing in High moisture area

3 Specification

- ASTM C 920 Type S, Class 25
- JIS Z2911
- JIS A 5758-04 G 20LM
- *1 Standard Specification for Elastomeric Joint Sealants

4 Color

Translucent/White/Black/Gray/Light gray/Dark brown/Dark Ivory/Ivory/Stone beige/Pewter/Off white/Brown

5 Packing 300ml/cartridge

6 Properties



Properties			Results	Test Method
Before curing	Appearance		Paste	=0
	Fluidity		Non-Sagging	
	Skin-Over Time at 23°C/50%RH	min	5	
After curing	Density @ 23 degree C	g/cm³	1.05	JIS K-6249
	Hardness shore A		17	JIS K-6249
	Tensile Strength	МРа	1.4	JIS K-6249
	Elongation at break	%	620%	JIS K-6249

Curing conditions: 23-25 degree Celsius, 50-55% humidity, 7 days



7 Instruction for use

Please read the latest Shin-Etsu published Functional Sealants Technical Manual. The manual can be obtained from the Shin-Etsu website. http://www.shinetsusilicone-global.com/

B Handling Precautions

- It reacts with moisture in the air and begins to cure at the surface. Consequently, the cure speed will vary according to the temperature and humidity of environment.
- Please note that it may not cure if it comes in contact with flux or certain materials.
- When using with air gun, be sure to set the pressure at a safe and proper level. Pressure should be exceeded 0.2-0.3 MPa.

9 Limitation

- 1) Do not use for structural glazing
- It may cause corrosion and discoloration on galvanized iron, zinc-coated steel, copper, brass, limestone, cement, concrete, brick, marble and other porous materials, etc.
- 3) Appropriate for movement joints maximum ±25%

- Before using, the prior test on materials are recommended
- 5) It can't be used as aquarium sealing and interior fire stop system applications.
- 6) Do not use with reflective coated mirrors
- 7) Do not use with direct food and drinking water contact application

10 Storage Precaution

• Stored between 1-25°C and keep out of sunlight.

11 Shelf Life

12 month from manufacturing date under storage condition in No. 10

12 Safety and Hygiene

- Be sure to provide adequate ventilation area when using
- Be careful not to rub the eyes with hands when using.
 Please take the appropriate wearing glasses.
- Keep out of children
- Please read Material Safety Data Sheet(MSDS) before using.

Shin-Etsu Chemical Co., Ltd.

Silicone Division Sales And Marketing Department IV

6-1, Otemachi 2-chome, Chiyoda-ku, Tokyo, Japan Phone: +81-(0)3-3246-5153 Fax: +81-(0)3-3246-5365

Shin-Etsu Silicone Korea Co., Ltd.

GT Tower 15F, 411, Seocho-daero, Seocho-gu, Seoul 06615, Korea Phone: +82-(0)2-590-2500 Fax: +82-(0)2-590-2501

Shin-Etsu Silicone International Trading (Shanghai) Co., Ltd.

29F Junyao International Plaza, No.789, Zhao Jia Bang Road, Shanghai 200032. China

Phone: +86-(0)21-6443-5550 Fax: +86-(0)21-6443-5868

Shin-Etsu Silicone (Thailand) Ltd.

 7^{th} Floor, Harindhorn Tower, 54 North Sathorn Road, Bangkok, 10500, Thailand

Phone: +66-(0)2-632-2941 Fax: +66-(0)2-632-2945

Shin-Etsu Singapore Pte. Ltd.

4 Shenton Way, #10-03/06, SGX Centre II, Singapore 068807

Phone: +65-6743-7277 Fax: +65-6743-7477

- The data and information presented in this catalog may not be relied upon to represent standard values. Shin-Etsu reserves the right to change such data and information, in whole or in part, in this catalog, including product performance standards and specifications without notice.
- Users are solely responsible for making preliminary tests to determine the suitability of products for their intended use. Statements concerning possible or suggested uses made herein may not be relied upon, or be construed, as a guaranty of no patent infringement.
- The silicone products described herein have been designed, manufactured
 and developed solely for general industrial use only; such silicone product are
 not designed for, intended for use as, or suitable for, medical, surgical or
 other particular purposes. Users have the sole responsibility and obligation to
 determine the suitability of the silicone products described herein for any
 application, to make preliminary tests, and to confirm the safety of such
 products for their use.
- Users must never use the silicone products described herein for the purpose of implantation into the human body and/or injection into humans.
- Users are solely responsible for exporting or importing the silicone products described herein, and complying with all applicable laws, regulations, and rules relating to the use of such products. Shin-Etsu recommends checking each pertinent country's laws, regulations, and rules in advance, when exporting or importing, and before using the products.
- Please contact Shin-Etsu before reproducing any part of this catalog.
 Copyright belong to Shin-Etsu Chemical Co., Ltd.

http://www.shinetsusilicone-global.com



The Development and Manufacture of Shin-Etsu Silicones are based on the following registered international quality and environmental management standards.

008 ISO 9001 ISO 14001



